

# Manual of Digital Thermo-hygrometer CH-910

## 一、 Specifications:

Temperature range: -10°C-50°C (14°F ~ 122°F)

Humidity range: 10%-99%

Temperature error: 0°C~40°C: ±1°C Others : ±2°C

Humidity error : ±3% at 25°C 40%~80%; Others±5%

Resolution: Temperature 0.1°C Humidity 1% RH

Sampling time: 10s

Unit size: 93.5×114.5×22mm

N.W.: 130g

Power supply: 1\*1.5V (AAA) battery

## 二、 Features:

- 1、 Large LCD display temperature, humidity, max/min , comfort level.
- 2、 Touch button control
- 3、 Comfort level function, more intuitive and considerate.
- 4、 LED backlight function, more convenient to use the product at night.
- 5、 Temperature °C / °F switch function, can choose display Celsius or Fahrenheit to meet different people's habits.
- 6、 Have stand holder and hanging hole at the back, can be placed standing or hanging.
- 7、 Low power consumption, high precision and high stability.

## 三、 Operation Instruction:

Open the battery tank and take out the insulator( install the battery), a beep means the product is powered on and start work.

- 1、 Clear: Clear Max Min Memory;
- 2、 C/F: Switch C/F temperature;
- 3、 Light: The backlight will turn off without any key operation after 30s.
- 4、 LCD ON/OFF: Turns the LCD on or off. Buttons (1/2/3) are invalid when LCD is off;
- 5、 Reset: The product restore to initial state

### \*Notes:

- 1、 When the font display becomes faint, it mean the battery is low and need change new battery.
- 2、 The function need to be reset and MAX/MIN memory be cleared when battery changed.